

BRACKET SOLUTIONS WORKSHEET

CONTACT INFORMATION

Company: _____ Phone: _____

Contact: _____ Email: _____

CABINET INFO

Drill Pattern:

- X= 3.5 mm X= 0 mm X= 16 mm X= 3.5 mm X= 3.5 mm
 Y= 16 mm Y= 3 mm Y= 3.5 mm Y= 8 mm Y= 3 mm


Dowel Diameter:

- 8 mm 10 mm Screw-On Peninsula

Slide Type:

- Undermount Roller Undermount Ball Bearing Sidemount

Back Thickness: _____




Determine Bracket Space

(measurement between slide and the back panel)

Calculate as follows: **A - B - C = D**

- A (inside cabinet depth)
- B (Slide set back)
- C (nominal slide length)
- D (min. & max. bracket space)

A: MINUS **B:** MINUS **C:** EQUALS **D:**



For more Information or any Questions, please contact Tenn-Tex

sales@tenntex.com
 1-800-TENN-TEX / 336-931-1100
 336-931-1110 (fax)
www.tenntex.com



TENN-TEX
PLASTICS INC.

MADE IN THE USA

Slide	Abbr	Lengths	Setback
Accuride 3832 (Ball Bearing)	ACC	450, 500, 550, 400, 350	3
AMS (Sidemount)	AMS	582, 500	2
Blum SOLO (Roller Undermount)	Blum Solo	571, 494, 418, 342, 266	4
Blum Tandem (Undermount)	BL	546, 470, 394, 317	4
Ferrari (Ball Bearing)	FER	559, 508, 457, 406, 356, 305, 254	3
Fulterer 5000 (Ball Bearing)	F5000	450, 500, 550, 400, .50, 300, 250	3
Fulterer 5043 (Ball Bearing)	F5043	450, 500, 550, 400, 350, 300, 250	3
Grass 6603 (Sidemount)	GR	582, 570, 550, 500, 431.5	2
Grass Dynapro (Undermount)	DYN	545, 469, 393, 318, 260	4
Grass Elite (Undermount)	GR	550, 470, 394, 317, 250	4
Grass Express (Roller Undermount)	GR Exp	575, 500, 422, 344, 270	1.5
Hafele Moovit (Undermount)	HAF-MOOVIT		
Hettich 5632 (Ball Bearing)	HET-5632	350, 400, 500, 550, 600, 650, 700, 250, 300	2
Hettich FAQ (Undermount)	HET-FAQ	574, 498, 422, 345, 269	
Hettich Quadro (Undermount)	HET-Quad	546, 394, 470, 318, 242	2
HGH (Ball Bearing)	HGH	450, 500, 550, 400, 350, 300, 250	3
Knape & Voigt 8400 (Ball Bearing)	KV	559, 508, 457, 406, 356, 305, 254	3
Knape & Voigt MUV (Undermount)	KV	569, 544, 518, 467, 417, 391, 366, 315, 258	2
Salice (Sidemount)	SAL	500, 550, 570	2
Salice Adar (Undermount)	SAL	543, 467, 391, 315	4
Top Slide CC447 (Undermount)	Top Slide	540, 490, 440, 390, 340, 290	3